

Airless bottle refill system offering innovation in both design and functionality



RPM-420NJ
M-Cap with inner ring
(for refill bottle)

RPM-420NJ
RPM-420NJ CASE
PD-2028EBII Z Pump



Lightweight refill bottle collapses with use

The refill bottle collapses along the creases, allowing formula to be dispensed more completely



Bottle is replaced with a single click

Quick and easy replacement of the refill in the reusable case



Pump and outer case are kept for repeated use

Open design makes it easy to check the remaining amount

Easy to use eco-friendly refill system



The pump is simply attached to the refill bottle and clipped into the outer case. The innovatively designed case can be used repeatedly, and only the lightweight refill bottle is replaced.


01 Remove the used refill bottle from outer case.

02 Remove the cap of the refill container and attach the pump.

03 Make sure the pump is tightly assembled, and slide the bottle into outer case to complete the process.

Collapses along creases & airless structure prevents contact with air

The airless structure preserves the freshness of the contents by preventing contact with air. Thanks to its unique design, the bottle collapses uniformly along its creases, making it possible to visually confirm how much formula remains.



RPM-420NJ Assembled

Total height : 206mm
Body diameter : 89mm
Accessory : PD-2028EBII Z (Dose : 2cc)

RPM-420NJ

Total height : 151mm
Body diameter : 75mm
Material : HDPE+LDPE
Filling volume : 420ml

RPM-420NJ CASE

Total height : 165mm
Body diameter : 89mm
Material : PP

PD-2028EBII Z Pump

Total height : 96mm
Width : 33mm
Dose : 2cc

M-Cap with inner ring (for refill bottle)

Total height : 20mm
Width : 32mm
Material : PP